

SKU SP-A390-VG-QD Job Name: Mark: Submitted By: Date: 04/25/2025

Bathroom Exhaust Fan, Model SP-A390-VG, 115/208-230/277V, 1Ph, 93-410 CFM




Model SP-A direct drive, ceiling mounted fan is designed to provide the lowest sounds levels for bathroom exhaust. Units feature an insulated housing and are ideal for residential, multi-family or hotel applications. Model CSP-A390-VG features a tri-voltage design to operate at 115/208-230/277V. Vari-Green EC motor technology included for maximum fan controllability.


- ENERGY STAR rated
- Acoustic insulation absorbs sound ensuring quiet operation
- Spring loaded aluminum backdraft damper eliminates rattling
- External electrical access reduces installation time
- Speed controllable
- Designer grille included

Certifications

AMCA Air & Sound UL/cUL 507



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel				
Drive Type	Direct Drive				
Impeller Type	Centrifugal Wheel				
Impeller Material	Polypropylene				
Includes	Backdraft damper				
	Mounting brackets				
Certifications	AMCA Air & Sound				
Certifications	UL/cUL 507				
Speed Controllable	Yes				

Motor Information

Motor Phase	1					
Voltage	115/208-230 277					
Motor Enclosure	Totally Enclosed Non- Vented					
RPM	1750					
Motor Included	Yes					

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.1	0.125	0.25	0.375	0.5	0.625	0.75	0.875	1
47 93	005	005	CFM	276	251	248	233	215	196	173	146	120	93
	935	935	Sones	2	2	2	2.5	3	3.5	4	5	6	6
100	1340	1340	CFM	410	395	390	370	361	349	338	325	307	294
			Sones	5	5	5	5	5	6	6.5	7	7	7

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov