

SKU SQ-90-VG1X-QD Job Name: Mark: Submitted By: Date: 04/28/2025

Centrifugal Inline Fan, Product # SQ-90-VG1X-QD, 188-821 CFM




Model SQ, direct drive centrifugal inline fans feature a unique combination of installation flexibility, rugged construction, ease of service, high efficiency and low sound levels. These compact fans are ideal for indoor clean air applications including exhaust, return or make-up where space is a prime consideration.


- Compact size for height-restricted areas
- Composite backward inclined, non-overloading centrifugal wheel design
- Energy efficient, Vari-Green motor for maximum motor controllability.
- Inlet and discharge duct collars for easy duct connection
- Removable access panels permit easy access to interior components for cleaning and servicing

Certifications

AMCA Sound & Air Performance UL/cUL 705



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel			
Drive Type	Direct Drive			
Impeller Type	Centrifugal Wheel			
Impeller Material	Aluminum			
Includes	Access Panel			
	Disconnect switch			
	AMCA Sound & Air			
Certifications	Performance			
	UL/cUL 705			
Speed Controllable	Yes			

Motor Information

Motor Insulation	В				
Motor Phase	1				
Motor Type	BrushlessDC				
Service Factor	1				
Voltage	115 208 230 277				
HP	1/10				
Hertz	60				
Motor Enclosure	n/a				
RPM	1800				
Thermal Protection	AutoOverload				
Nominal Efficiency	85				

Air and Sound Performance

Motor HP	Max BHP	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625
1/10 0.02	0.00	0.02 1050	0	CFM	500	370	188	-	-	-
	0.02			Sones	4	3.9	4.1	-	-	-
1/10 0.04	0.04	.04 1300	0	CFM	619	519	398	245	-	-
	0.04			Sones	5.4	5.4	5.5	5.5	-	-
1/10	0.07	1550	0	CFM	738	655	565	457	334	-
	0.07			Sones	7.6	7.5	7.4	7.4	7.4	-
1/10	0.09	1725	0	CFM	821	748	669	579	481	366
				Sones	8.8	8.8	8.7	8.8	8.8	8.9



- Greenheck Fan Corporation certifies that the model shown herein is licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- Performance certified is for installation type B: Free inlet, Ducted outlet.
- Power rating (BHP/kW) does not include transmission losses.
- Performance ratings do not include the effects of appurtenances (accessories).
- The inlet sound ratings shown are loudness values in fan sones at 5 ft. (1.5 m) in a hemispherical free field calculated per AMCA Standard 301. Values shown are for installation type B: free inlet hemispherical sone levels.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov