



SKU  
CSP-A125-QD

Job Name:  
Mark:  
Submitted By:  
Date: 04/27/2025

## Inline Cabinet Fan, Product # CSP-A125-QD, 91-138 CFM




Model CSP inline fans are high performance fans designed for exhaust, supply or return air applications where low sound level are required. Units feature an insulated, galvanized steel housing with a forward-curved wheel.

- 11.875 x 7.625 inch inlet width x height
- 8 x 6 inch outlet width x height
- Speed controllable, with up to 30% turndown


### Certifications

AMCA Air  
UL/cUL 507



A	B	C	D	E	F	G
13.25 in	10.625 in	9 in	8 in	6 in	12 in	9.25 in

### Performance Characteristics



### Construction Features

Housing Material	Galvanized Steel
Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Includes	Access Panel Backdraft damper Mounting brackets
Certifications	AMCA Air UL/cUL 507
Speed Controllable	Yes

### Motor Information

Motor Insulation	A
Motor Phase	1
Motor Type	PSC
Service Factor	1
Voltage	115
Hertz	60
Motor Enclosure	n/a
RPM	1100
Thermal Protection	AutoOverload
Nominal Efficiency	30
Watts	20.4

### Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375
23	1100	880	CFM	138	124	114	91
			Sones	1.6	1.5	1.6	1.8



- Greenheck Fan Corporation certifies that the CSP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and comply with the requirements of the AMCA Certified Ratings Program.
- The CSP models are not AMCA certified with 50 hertz motors.

## California Residents

### WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)